


Transport equipment

Product data sheet

Article no.: B9125V ESD-Tubular steel truck



ESD-tubular steel truck with steel sheet blades, sturdy welded construction, electrically conductive powder coating, slate grey RAL 7015. ESD-Safety grips. Steel sheet front shovel screwed on, therefore exchangeable. ESD-solid rubber tyres on synthetic rims, hubs with roller bearings. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc.

Technical Details:



Total load capacity (kg)	200
Blade width (mm)	320
Blade depth (mm)	250
Total width (mm)	570
Total depth (mm)	533
Total height (mm)	1150
Tyres	Solid rubber-ESD
Wheel size (mm)	260 x 56
Weight (kg)	14,8
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976191256