## **Product data sheet**

Article no.: TK1328 Stairway truck steel



**Transport equipment** 



Tubular steel, with lifting blades made of steel plate, sturdy welded construction, powder coated, blue RAL 5007. Safety handles. With 2 pneumatic tyres on synthetic rims, hubs with roller bearings and 2 five-armed wheel spiders, each equipped with 5 TPE wheels 125 mm Ø, hubs with bush bearings. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Steel sheet front shovel mountable. Flat packed delivery.

## **Technical Details:**







Total load capacity (kg)	200
Blade width (mm)	480
Blade depth (mm)	300
Total width (mm)	590
Total height (mm)	1300
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Version	für gelegentliche Treppenfahrten
Weight (kg)	22
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976113289