

KERN CD100-2P2

Load cells made of stainless steel



Packaging & shipping

Delivery:	864 h
Dimensions packaging (WxDxH):	220 x 220 x 160 mm
Gross weight:	2,700 kg
Net weight:	2,200 kg
Shipping method:	Parcel service

Construction

Cable length:	20 m
---------------	------

Piktogramme

STANDARD



Measuring system

Combined Error:	0,030 %
Load cell connection:	4-wire
Nominal sensitivity:	1,500
OIML class:	C2
Resolution Load cell à Verifiable:	2000 e
Weighing capacity [Max]:	100 t
Y value:	5000

Environmental conditions

Maximum operating temperature:	65 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-35 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------