

KERN KFP60V20LM

Platform with stainless steel weighing plate and IP65



Piktogramme

STANDARD



FACTORY



Measuring system

Load cell connection:	4-wire
Readability [d]:	2 g
Weighing capacity [Max]:	30 kg 60 kg

Technical data about verification

Minimum load [Min]:	200 g 400 g
Verification by KERN possible:	yes
Verification value [e]:	10 g 20 g

Service

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	930 x 550 x 210 mm
Gross weight:	15,900 kg
Net weight:	13,300 kg
Shipping method:	Parcel service

Construction

Cable length:	2,500 m
Dimensions of weighing plate (WxDxH):	500 x 400 x 137 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	500 x 400 mm