

KERN HB0100-0.

Compact handheld durometer with drag indicator

KERN[®]



Measuring system

Precision (of [Max]):	3 %
Readability:	1
Weighing units:	Shore A0

Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C

Category

Brand:	Sauter
Category:	Hardness testers

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	147 x 95 x 52 mm
Gross weight:	480 g
Net weight:	160 g
Shipping method:	Parcel service

Construction

Casing material:	metal
Dimensions (WxDxH):	115 x 60 x 25 mm
Dimensions housing (WxDxH):	115 x 60 x 25 mm
Overall dimensions mounted (WxDxH):	115 x 60 x 25 mm

Piktogramme

STANDARD

