

# KERN IXS100K-3L



Platform scale with stainless steel display device with IP68 rating, XL display und EC type approval [M] â now also as high resolution version with high-resolution display



Weighing with tolerance range: yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

## Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter/adaptor included:	EURO
Operating time (Backlight off):	80 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional (factory)

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

## Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	590 x 925 x 245 mm
Gross weight:	38 kg
Net weight:	35 kg
Shipping method:	Freight forwarder

## Construction

Cable length of display device:	2,500 m
Dimensions of display device (WxDxH):	232 x 150 x 80 mm
Dimensions of weighing plate (WxDxH):	650 x 500 x 133,5 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	650 x 500 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	15 g
Number of weighing ranges:	1
Readability [d]:	5 g
Recommended adjusting weight:	150 kg (M1)
Repeatability:	5 g
Resolution:	30000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-150 kg
Warm up time:	2 h
Weighing capacity [Max]:	150 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height: 5,500 cm

## Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	5 g
Minimum piece weight at piece counting (Normal):	50 g

## Functions

Counting function:	yes
Data hold function:	yes
Help function on the display:	yes
Peak function:	yes
PRE-TARE function:	yes
Vibration-free weighing (Animal weighing program):	yes

# KERN IXS100K-3L



Platform scale with stainless steel display device with IP68 rating, XL display und EC type approval [M] â now also as high resolution version with high-resolution display

## Piktogramme

### STANDARD



### OPTION



### FACTORY

