

3M[™] DOUBLE-SIDED TAPES FOR HARD-TO-BOND TEXTURES WITH 3M[™] ACRYLIC ADHESIVE 300MP

It's a textured world. Design for it.

Expect performance. Spec 3M.

3M[™] DOUBLE-SIDED TAPES FOR HARD-TO-BOND TEXTURES WITH 3M[™] ACRYLIC ADHESIVE 300MP



Performance means seamless control

High performance for the world's toughest environments.

Attach. Seal. Reduce noise. Expand your materials and your design possibilities. Double-sided tapes engineered with 3M[™] Acrylic Adhesive 300MP bond hard-to-bond textures in addition to a range of other materials, even when exposed to UV, humidity and more. It's tough out there. Make sure your design lasts.

Durability means repetitive handling won't wear it down

Versatility means luxury without compromise 3M[™] DOUBLE-SIDED TAPES FOR HARD-TO-BOND TEXTURES WITH 3M[™] ACRYLIC ADHESIVE 300MP

SPECIALTY VEHICLE APPLICATION

Daredevil-proof design.

Advanced adhesives keep it together under the harshest of conditions, while you feel the thrill of defying creative limitations.



Upholstery material

- 3M[™] Double Coated Tape 99786

High-density foam 3M[™] DOUBLE-SIDED TAPES FOR HARD-TO-BOND TEXTURES WITH 3M[™] ACRYLIC ADHESIVE 300MP

OFFICE LAYOUT APPLICATION

Make workspaces work well.

Build soundproofing into cubicle walls — and let your attention to detail be known.



Attach fabric to metal with 3M[™] Double Coated Tape 9832HL **GENERAL INDUSTRIAL APPLICATION**

Strength where it matters most.


Make it stick, no matter what. Design for almost any application and rest assured you've got a bond you can count on.



Attach nylon denier to plastic with 3M[™] Adhesive Transfer Tape 6035PC

AUTOMOTIVE APPLICATION Keep passengers cool.

Design with comfort in mind. Anti-lifting adhesives conform firmly to curves on breathable fabrics, making every ride feel like a luxury.






Attach seat foam to polyurethane film with 3M[™] Adhesive Transfer Tape 6035PC

HVAC APPLICATION

Support heating and cooling efficiency.

Enhance any indoor environment — and your design toolkit — with gasket-sealing adhesives that won't leak or rattle.



Attach closed-cell foam to galvanized steel with 3M[™] Double Coated Tape 9832HL

Warine Application Weather the waves.

Steer your concept toward success with adhesives that attach protective surfaces — and keep the adventure going strong.



Attach EVA foam boat decking to fiberglass with gelcoat with 3M[™] Adhesive Transfer Tape 9775WL

More materials. More design possibilities.

- High-performance versatility
- Excellent adhesion to foam, fabric, felt, nylon, carpet, leather, fiberglass and wood
- Dimensional stability and improved handling
- High shear strength on textured or rough substrates in addition to other materials


- Ease of die-cutting and laminating
- High initial tack
- Perfect for a variety of markets, including general industrial, automotive, marine, medical equipment, specialty vehicle and construction finishing

Hard-to-bond textures

- Polyurethane foam
- Microcellular urethane foam
- Polyethylene foam
- EPDM foam
- Textiles/fabric
- ► Felt
- ► Vinyl
- ► Wood

- Particle board
- Plywood
- Melamine
- Nylon
- Carpet
- Leather
- ► Fiberglass

Tape strength comparison



The value of the y-axis is related to the amount of foam tear during the peel procedure. The higher the value, the more foam tear.

3M[™] High Performance Acrylic Adhesive Product Selection

with 3M[™] Acrylic Adhesive 300MP

300MP Double Coated Tapes

Product Number	Primary Liner	Adhesive I Caliper	Carrier Type	Adhesive II Caliper	Total Tape Caliper
3M [™] Double Coated Tape 9832HL	83# PCK Paper 6.2mil [0.16mm]	2.3mil [0.058mm]	Clear PET Film .5mil [.013mm]	2.0mil [0.051mm]	4.8mil [0.12mm]
3M [™] Double Coated Tape 99786	58# PCK Paper 4.2mil [.106mm]	2.75mil [0.07mm]	Non-woven Scrim	2.75mil [0.07mm]	5.5mil [0.14mm]

300MP Adhesive Transfer Tapes

Product Number	Primary Liner	Adhesive I Caliper	Total Tape Caliper
3M [™] Adhesive Transfer Tape 9772WL	96# PCK Paper 7.0mil [0.18mm]	2.0mil [0.051mm]	2.0mil [0.051mm]
3M [™] Adhesive Transfer Tape 9773WL	96# PCK Paper 7.0mil [0.18mm]	3.0mil [0.076mm]	3.0mil [0.076mm]
3M [™] Adhesive Transfer Tape 9774WL	96# PCK Paper 7.0mil [0.18mm]	4.0mil [0.102mm]	4.0mil [0.102mm]
3M [™] Adhesive Transfer Tape 9775WL	96# PCK Paper 7.0mil [0.18mm]	5.0mil [0.127mm]	5.0mil [0.127mm]
3M [™] Adhesive Transfer Tape 6035PC	58# PCK Paper 4.2mil [.106mm]	5.0mil [0.127mm]	5.0mil [0.127mm]





Solventless Technology: 3M[™] Acrylic Adhesive 300MP is made with a solventless technology.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

© 3M 2018. All rights reserved. 3M is a trademark of 3M Company. 3M is a Responsible Tape Manufacturer, PSTC. Printed in U.S.A. 70-0713-4686-3



Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144 USA

Phone 1-800-362-3550 Web 3M.com/converter