

## CK 640 GORE BOA SF

**SAFETY BOOT EN ISO 20345:2011 S3 SRC CI HRO**  
**SIZES: 38 - 47 (240 - 307) | FITTING OPTIONS: NB, XB (S, XXB)**



**S3** **PROTECTION CLASS S3**  
according EN ISO 20345

**STEITZ FLEX-ZONE®**  
Outsole with flexion zone

**TEXTILE PUNCTURE RESISTANCE**  
highly flexible, metal free  
puncture resistance

**DGUV 191** **INSOLE TREATMENT**  
tested according to  
DGUV Rule 112-191

**BOA® FIT SYSTEM**  
for a fast, effortless, precision fit.

**ORIGINAL STEITZ MULTI-WIDTH SYSTEM**  
4 different widths per shoe size

**COMPOSITE TOE CAP**  
Metal free toe cap, made of  
composite materials

**ESD**  
Protection against electrostatic  
discharge

**GORE-TEX**  
Membrane system, waterproof and  
highly breathable

### FEATURES

- + GORE-TEX membrane
- + Full-grained, hydrophobic smooth leather combined with breathable textile inserts
- + BOA® Fit System
- + Dust guard tongue
- + Reinforced, abrasion-resistant toe guard
- + High visibility safety reflectors
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

### OUTSOLE

#### Perbunan CK ESD, grey-black

- + Outsole with a profile of 3 mm
- + Best possible anti-slip properties on slippery, wet or oily surfaces
- + Hard-wearing and excellent cut resistance
- + Flexion zone with pivot point
- + Broad contact surface
- + Durable against acid and oil-based substances
- + Heat-resistant up to approx. 220 °C, heat resistant in the short term up to approx. 300 °C



### CUSHIONING

#### Universal shock absorption

Universal shock absorption through soft-foamed PU midsole. Additionally, the removable and comfortably soft comfort insole provides best possible moisture transportation.

