

## CK 7620 PERBUNAN SF

**SAFETY BOOT EN ISO 20345:2011 S3 SRC CI**

**SIZES: 38 - 47 (240 - 307) | FITTING OPTIONS: NB, XB (S, XXB)**



**S3** **PROTECTION CLASS S3**  
according EN ISO 20345

**STEITZ FLEX-ZONE®**  
Outsole with flexion zone

**TEXTILE PUNCTURE RESISTANCE**  
highly flexible, metal free  
puncture resistance

**ESD**  
Protection against electrostatic  
discharge

**4** **ORIGINAL STEITZ MULTI-WIDTH SYSTEM**  
4 different widths per shoe size

**COMPOSITE TOE CAP**  
Metal free toe cap, made of composite  
materials

**METAL FREE**

**DGUV 191** **INSOLE TREATMENT**  
tested according to  
DGUV Rule 112-191

### FEATURES

- + Soft nubuck leather
- + Dust guard tongue
- + Reinforced, abrasion-resistant toe guard
- + Cushioned collar for additional comfort

- + Functional lining made of breathable textile and microfibre
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

### OUTSOLE

#### Perbunan CK ESD, grey-blue

- + Outsole with a profile of 3,6 mm
- + Light and flexible with tailored arch support
- + Flexion zone with pivot point
- + Cushioning structure in the heel area
- + Best possible scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 220 °C



### CUSHIONING

#### Universal shock absorption

Universal shock absorption through soft-foamed PU midsole. Additionally, the removable and comfortably soft comfort insole provides best possible moisture transportation.

