

ESD CK POLAR SF

SAFETY WINTER BOOT EN ISO 20345:2011 S3 SRC CI
SIZES: 38 - 47 (240 - 307) | FITTING OPTIONS: NB, XB (S, XXB)



S3 **PROTECTION CLASS S3**
according EN ISO 20345

STEITZ FLEX-ZONE®
Outsole with flexion zone

TEXTILE PUNCTURE RESISTANCE
highly flexible, metal free
puncture resistance

INNER LINING
warm winter lining,
good thermal insulation

4 **ORIGINAL STEITZ MULTI-WIDTH SYSTEM**
4 different widths per shoe size

COMPOSITE TOE CAP
Metal free toe cap, made of composite
materials

ESD
Protection against electrostatic
discharge

FEATURES

- + Soft nubuck leather combined with oily nubuck leather
- + Outsole flexible at low temperatures up to approx. -25 °C
- + Velcro fastening strap
- + Dust guard tongue
- + Centered lacing
- + Lambskin lining
- + Cold insulating
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

OUTSOLE

Perbunan CK ESD, grey-black

- + Outsole with a profile of 3 mm
- + Best possible anti-slip properties on slippery, wet or oily surfaces
- + Hard-wearing and excellent cut resistance
- + Flexion zone with pivot point
- + Broad contact surface
- + Durable against acid and oil-based substances
- + Heat-resistant up to approx. 220 °C, heat resistant in the short term up to approx. 300 °C



CUSHIONING

Universal shock absorption

Universal shock absorption through soft-foamed PU midsole. Additionally, the removable and comfortably soft comfort insole provides best possible moisture transportation.

