

ESD DX 741 SF

SAFETY SHOE EN ISO 20345:2011 S1P SRC

SIZES: 36 - 48/49 (225 - 315) | FITTING OPTIONS: NB, XB (S, XXB)



- | | |
|--|---|
|  PROTECTION CLASS S1P
according EN ISO 20345,
additional puncture resistance |  ORIGINAL STEITZ MULTI-WIDTH SYSTEM
4 different widths per shoe size |
|  STEITZ FLEX-ZONE®
Outsole with flexion zone |  ALUMINIUM TOE CAP
Toe cap made of aluminium |
|  TEXTILE PUNCTURE RESISTANCE
highly flexible, metal free
puncture resistance |  ESD
Protection against electrostatic
discharge |

FEATURES

- + Ultra-lightweight microfibre
- + Perforation for optimal ventilation
- + High visibility safety reflectors
- + Functional lining made of breathable textile and microfibre
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

OUTSOLE

TPU Dynamics ESD, white

- + Outsole with a profile of 2,6 mm
- + Light and flexible with tailored arch support
- + Flexion zone with pivot point
- + Cushioning structure in the heel area
- + Best possible scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 120 °C



CUSHIONING

Universal shock absorption

Universal shock absorption through soft-foamed PU midsole. Additionally, the removable and comfortably soft comfort insole provides best possible moisture transportation.

