

ESD DX 782 SF

SAFETY BOOT EN ISO 20345:2011 S3 SRC

SIZES: 36 - 48/49 (225 - 315) | FITTING OPTIONS: NB, XB (S, XXB)



S3 **PROTECTION CLASS S3**
according EN ISO 20345

4 **ORIGINAL STEITZ MULTI-WIDTH SYSTEM**
4 different widths per shoe size

STEITZ FLEX-ZONE®
Outsole with flexion zone

AL **ALUMINIUM TOE CAP**
Toe cap made of aluminium

SF **TEXTILE PUNCTURE RESISTANCE**
highly flexible, metal free
puncture resistance

ESD
Protection against electrostatic
discharge

FEATURES

- + Soft nubuck leather
- + High visibility safety reflectors
- + Cushioned collar for additional comfort
- + Functional lining made of breathable textile and microfibre
- + Soft vamp-lining made of real leather
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

OUTSOLE

TPU Dynamics ESD, silvergrey

- + Outsole with a profile of 2,6 mm
- + Light and flexible with tailored arch support
- + Flexion zone with pivot point
- + Cushioning structure in the heel area
- + Best possible scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 120 °C



CUSHIONING

Universal shock absorption

Universal shock absorption through soft-foamed PU midsole. Additionally, the removable and comfortably soft comfort insole provides best possible moisture transportation.

