

## NF 696 S3 QRS

**WELDING BOOT EN ISO 20349:2010 SRC FE AI HI-1 WRU FO HRO**

**SIZES: 38 - 48/49 (240 - 315) | FITTING OPTIONS: NB, XB (XXB)**



**S3** PROTECTION CLASS S3  
according EN ISO 20345

**ST** STEEL TOE CAP  
Toe cap made of steel

**1** STEEL MIDSOLE  
puncture resistant steel midsole

**LEATHER-INSOLE**

**DGUV 191** INSOLE TREATMENT  
tested according to  
DGUV Rule 112-191

### FEATURES

- + Aluminised smooth leather
- + Quick-Removal-System
- + Functional grip
- + Fire resistant NOMEX® yarn
- + Ankle protection
- + Soft vamp-lining made of real leather
- + Comfort insole with heat-resistant aluminium coating

### OUTSOLE

- Perbunan Zermatt**, anthracite
- + Outsole with a profile of 7,0 mm
  - + Best possible anti-slip properties on slippery, wet or oily surfaces
  - + Hard-wearing and excellent cut resistance
  - + Broad contact surface
  - + Durable against acid and oil-based substances
  - + Heat-resistant up to approx. 220 °C



### CUSHIONING

#### Universal shock absorption

Universal shock absorption through soft-foamed PU midsole. Additionally, the removable and comfortably soft comfort insole provides best possible moisture transportation.

