


Transport equipment

Product data sheet

Article no.: 2035A Tyre truck



Welded, powder coated, surface durably protected, resistant to impact and scratches. Wheels with pneumatic tyres. Hubs with roller bearings. By activating the hand grips, the truck spreads its carrier spars so that the piles of tyres can be taken up and down directly. The pick up rolls at the tip of the carrier spar support and make the process easier. Suitable for tyres from 450 to 860 mm Ø. Up to 8 wheels and tyres possible.

Technical Details:



Total load capacity (kg)	200
Blade width (mm)	500-945
Blade depth (mm)	660
Total width (mm)	730
Total depth (mm)	1142
Total height (mm)	1510
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Version	for tyre diameter 450 - 860 mm
Weight (kg)	26
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976920351