


**Transport equipment**

# Product data sheet

Article no.: 4433 Trolley for sheet material



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platform made of derived timber material board, surface covered with corrugated rubber. Bolted tubular steel superstructure. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Effective height: 1050 mm, Height retaining bracket: 300 mm.

## Technical Details:



|  |   |
|--|---|
| <b>Total load capacity (kg)</b>        | 600   |
| <b>Length of usable platform (mm)</b>  | 1270  |
| <b>Width of usable platform (mm)</b>   | 535   |
| <b>Height of loading platform (mm)</b> | 271   |
| <b>Total length (mm)</b>               | 1270  |
| <b>Total width (mm)</b>                | 810   |
| <b>Total height (mm)</b>               | 1321  |
| <b>Tyres</b>                           | TPE   |
| <b>Wheel size (mm)</b>                 | 200 x 40  |
| <b>Note</b>                            | Support height: 1050 mm, height retaining bracket: 300 mm |
| <b>Weight (kg)</b>                     | 43  |
| <b>Country of origin</b>               | Germany   |
| <b>Warranty (years)</b>                | 10  |
| <b>Customs tariff number</b>           | 87168000  |
| <b>GTIN</b>                            | 4017976844336   |