


Transport equipment

Product data sheet

Article no.: 5792 Box cart



Box cart in angle steel construction with tubular handlebar, powder coated. Ends, 1 side and roof covered with galvanized 1 mm steel sheet. Double wing door made of angle steel filled with polycarbonate panel, with vertical locking rod and integrated cylinder lock. 1 fixed and 4 detachable wood material shelves, surface beech grain. 2 swivel and 2 fixed-wheel castors with TPE tyres (thermoplastic elastomer), hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking (trackless). TOTALSTOP central braking system standard on swivel castors. Clearance between shelves 280 mm. Capacity per shelf 90 kg.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1000
Width of usable platform (mm)	680
Shelf heights (mm)	292, 582, 882, 1182, 1482
Load capacity per shelf (kg)	90
Total length (mm)	1170
Total width (mm)	745
Total height (mm)	1792
Tyres	TPE
Wheel size (mm)	200 x 40
Version	transparenter Kunststoff mit Treibriegelverschluss
Weight (kg)	151
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976957920