


Transport equipment

Product data sheet

Article no.: B1115P Tubular steel truck



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Punctureproof PU-tyres on synthetic rims, hubs with roller bearings. Flat packed delivery.

Technical Details:



| | |
|---------------------------------|-----------------------|
| Total load capacity (kg) | 250 |
| Blade width (mm) | 400 |
| Blade depth (mm) | 150 |
| Total width (mm) | 590 |
| Total depth (mm) | 506 |
| Total height (mm) | 1150 |
| Tyres | Polyurethane material |
| Wheel size (mm) | 260 x 85 |
| Weight (kg) | 12,7 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976131115 |