


**Transport equipment**

# Product data sheet

Article no.: B1215P Tubular steel truck



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Punctureproof PU-tyres on synthetic rims, hubs with roller bearings. Flat packed delivery.

## Technical Details:



<b>Total load capacity (kg)</b>	300
<b>Blade width (mm)</b>	450
<b>Blade depth (mm)</b>	150
<b>Total width (mm)</b>	620
<b>Total depth (mm)</b>	565
<b>Total height (mm)</b>	1200
<b>Tyres</b>	Polyurethane material
<b>Wheel size (mm)</b>	260 x 85
<b>Weight (kg)</b>	16,7
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976131146