


Transport equipment

Product data sheet

Article no.: B1327P Tubular steel truck



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Punctureproof PU-tyres on synthetic rims, hubs with roller bearings. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Flat packed delivery.

Technical Details:



Total load capacity (kg)	300
Blade width (mm)	320
Blade depth (mm)	250
Total width (mm)	580
Total depth (mm)	747
Total height (mm)	1600
Tyres	Polyurethane material
Wheel size (mm)	260 x 85
Weight (kg)	15,7
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976131184