Data Sheet



## Temflex™ 1800

### Vinyl Electrical Tape

### **Product Description**

Temflex™ 1800 Electrical Tape is a good quality and economical general purpose vinyl insulating tape. It has excellent resistance to: abrasion, moisture, alkalies, acid, and varying weather conditions (including sunlight). It is a polyvinyl chloride (PVC) tape that has a high wet dielectric strength, is conformable, and provides excellent mechanical protection with minimum bulk.

### **Applications**

Primary electrical insulation for all wire and cable splices rated up to 600 volts.

Protective jacketing for high voltage cable splices and repairs.

Harnessing of wires and cables.

For indoor or outdoor applications.

For above or below grade applications.

## Typical Data/Physical Properties

**Dielectric Strength\***Standard Condition

>1000 V/Mil

After Humidity
Condition >90% of Standard

**Insulation Resistance\*** 

>10<sup>6</sup> Megohms

**Thickness\*** 8 mils

Elongation\* 200%

**Breaking Strength\*** 20 lbs/in

Adhesion\*

To Steel 16 oz/in To backing 16 oz/in

\*ASTM D-1000

Note: These are typical properties and should not be used for specification purposes.

# **Installation Techniques**

The tape shall be applied in half-lapped layers with sufficient tension to conform and produce a uniform covering. In most applications, this tension will reduce the tape's width to approximately 5/8 of its original width. On pigtail splices, the tape should be wrapped beyond the end of the wires and then folded back, leaving a protective cushion to resist cut—through. Apply the tape with no tension on the last wrap to prevent flagging.

#### **Maintenance**

Temflex<sup>™</sup> 1800 Electrical Tape is stable under normal storage conditions.

### **Availability**

Temflex<sup>™</sup> 1800 Electrical Tape is available from 3M and your local 3M authorized electrical distributor.

#### **Important Notice**

All statements, technical information and recommendations related to the Seller's products are based on information believed to be reliable, but the accuracy or completeness thereof is not guaranteed. Before utilizing the product, the user should determine the suitability of the product for its intended use. The user assumes all risks and liability whatsoever in connection with such use.

Any statements or recommendations of the Seller which are not contained in the Seller's current publications shall have no force or effect unless contained in an agreement signed by an authorized officer of the Seller. The statements contained herein are made in lieu of all warranties, express or implied, including but not limited to the implied warranties of merchantability and fitness for a particular purpose which warranties are hereby expressly disclaimed.

SELLER SHALL NOT BE LIABLE TO THE USER OR ANY OTHER PERSON UNDER ANY LEGAL THEORY, INCLUDING BUT NOT LIMITED TO NEGLIGENCE OR STRICT LIABILITY, FOR ANY INJURY OR FOR ANY DIRECT OR CONSEQUENTIAL DAMAGES SUSTAINED OR INCURRED BY REASON OF THE USE OF ANY OF THE SELLER'S PRODUCTS THAT WERE DEFECTIVE.

(c)1991 3M

