



## Automotive Aftermarket Division

### 3M™ Blue Net Abrasive

---

#### 1) Part Numbers

<b>Discs</b>	
<b>Size 150 mm / 6", Disc on Roll</b>	
<b>36420</b>	3M™ Blue Net Disc, <b>80</b>
<b>36421</b>	3M™ Blue Net Disc, <b>120</b>
<b>36422</b>	3M™ Blue Net Disc, <b>150</b>
<b>36423</b>	3M™ Blue Net Disc, <b>180</b>
<b>36424</b>	3M™ Blue Net Disc, <b>220</b>
<b>36425</b>	3M™ Blue Net Disc, <b>240</b>
<b>36426</b>	3M™ Blue Net Disc, <b>320</b>
<b>Sheet Rolls</b>	
<b>Size 70 mm x 10 m, Sheet Roll</b>	
<b>36462</b>	3M™ Blue Net Sheet Roll, <b>80</b>
<b>36463</b>	3M™ Blue Net Sheet Roll, <b>120</b>
<b>36464</b>	3M™ Blue Net Sheet Roll, <b>150</b>
<b>36465</b>	3M™ Blue Net Sheet Roll, <b>180</b>
<b>36466</b>	3M™ Blue Net Sheet Roll, <b>220</b>
<b>36467</b>	3M™ Blue Net Sheet Roll, <b>240</b>
<b>36468</b>	3M™ Blue Net Sheet Roll, <b>320</b>
<b>Size 115 mm x 10 m, Sheet Roll</b>	
<b>36470</b>	3M™ Blue Net Sheet Roll, <b>80</b>
<b>36471</b>	3M™ Blue Net Sheet Roll, <b>120</b>
<b>36472</b>	3M™ Blue Net Sheet Roll, <b>150</b>
<b>36473</b>	3M™ Blue Net Sheet Roll, <b>180</b>
<b>36474</b>	3M™ Blue Net Sheet Roll, <b>220</b>
<b>36475</b>	3M™ Blue Net Sheet Roll, <b>240</b>
<b>36476</b>	3M™ Blue Net Sheet Roll, <b>320</b>



## 2) Description and Applications

Performance abrasive designed for use with a DA sander (or on a block). Product has very good initial and sustained cut for use on clear coats, paint, primer, filler, and plastics. Product designed to maximise extraction efficiency, when used with a dust extraction system.

Grade	Applications
80	General stock removal- Paint, Filler, Putty etc Used to clean the repair area and remove all loose paint particles or rust. Initial filler shaping.
120	Used to clean the repair area and remove all loose paint particles or rust. Filler sanding.
150	Used to clean the repair area and remove all loose paint particles or rust. Filler sanding.
180	Feather edge around the repair area.
220	Feather edge around the repair area. Surface refinement.
240	Surface refinement. Filler shaping. Levelling stone chips before repair.
320	Remove texture from primer surface. Final featheredging and refinement before primer application (Disc on Dual Action sander) E-coat sanding.

## 3) Physical Properties

Backing: Net with integrated loops  
Mineral: 3M™ Precision Shaped Grain and Aluminium Oxide blend  
Bonding: Resin Bond  
Colour: Blue  
Grades: 80 to 320

## 4) Directions for Use

Product can be used on a tool or by hand. Product should be used dry. For best results use in combination with a dust extraction system. Product does not require specific hole alignment, unlike traditional 15-hole discs.

## 5) Storage

It is recommended that all Coated Abrasive Products should be stored at constant levels of temperature and humidity within the ranges of 18-22°C, 50-65% RH. They should be kept away from damp (or cold) walls, windows, or floors to avoid possible moisture absorption. Equally storage adjacent to heat sources e.g. steam pipes, radiators, hot air ducts, ovens, etc. should be avoided. Product is best stored in original packaging until ready for use. Shelf Life indefinite under these conditions.

## 6) Safety

Whenever possible, sanding should be carried out in a well-ventilated area and it is strongly recommended that suitable goggles, dust mask and gloves are worn. Pads should not be modified in any way. They should be used only in their original size and shape, as supplied.

3M™ Blue Net Abrasives are designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.



# Technical Data Sheet

Effective: 01/07/2021 Supersedes: N/A

## 7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.

### For Additional Health and Safety Information

<b>3M United Kingdom plc</b> Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3Mbodyshop.co.uk">www.3Mbodyshop.co.uk</a>	<b>3M Ireland Limited</b> Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3Mbodyshop.co.uk">www.3Mbodyshop.co.uk</a>	<b>3M Denmark a/s</b> Automotive Aftermarket Hannemanns Allé 53 2300 København S  Tel: +45 43480100 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3MAuto.dk">www.3MAuto.dk</a>
<b>3M Finland, Suomen 3M Oy</b> Autotuotteet Keilaniementie 1 02151 Espoo Tel: 09 5252 1 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3M.fi/autotuotteet">www.3M.fi/autotuotteet</a>	<b>3M Svenska AB</b> Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3M.se/bileftermarkad">www.3M.se/bileftermarkad</a>	<b>3M Norge AS</b> Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3m.no/auto">www.3m.no/auto</a>
<b>3M Latvija</b> K.Ulmana 5 Rīga, LV-1004 Tel: +371 67066120 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3m.lv">www.3m.lv</a>	<b>3M Eesti OU</b> Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3m.ee">www.3m.ee</a>	<b>3M Lietuva</b> A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 <a href="mailto:aadukenquiries@mmm.com">aadukenquiries@mmm.com</a> <a href="http://www.3m.lt">www.3m.lt</a>

3M is a trademark of 3M Company, © 3M 2021, All rights reserved.