



Bemerkung - Note

Technische Daten - technical data
 Weight = 4.750 [kg]
 Torque max. (M1/M2) = 25 / 25 | 25 [Nm]
 Speed max. (n1/n2) = 8000 / 8000 | 8000 [1/min]
 Gear ratio (i)=n1:n2 = 1:1 | 1:1

Benennung - Title
Radial Bohr und Fräskopf
Radial drilling and milling head

EWS Tool Technologies
 EWS Weigle GmbH & Co. KG
 Maybachstr. 1
 D-73066 Uhingen
 www.ews-tools.de
 Nr. - No.
60.3025LDCTXTF

Technische Änderungen vorbehalten!
 Subject to technical modifications!
 IDENT: DEWS114.117
 MNR.
152729

