Series Soft-Faced Hammers





EAN: 4013288001375 **Size:** 280x95x32 mm

Part number:05000315001Weight:380 gArticle number:101Country of origin:CZ

Customs tariff 82052000

number:

- Powerful hammering with surface protection
- Soft-face hammers with hammer head out of nylon
- Suitable for sheet metal and renovation work as well as for tent, hall and fair booth construction jobs
- Inseparable and secure connection between the hammer handle and head
- · High-quality ashwood handle


Wera soft-face hammers. Double-sided conical design for a secure, inseparable connection between the hammer handle and head. The hammer head is made out of nylon; the handle out of high quality ash wood. Diverse applications thanks to the interchangeable soft-face hammer heads. Suitable for sheet metal and renovation work as well as for tent, hall and fair booth construction jobs.

Web link https://products.wera.de/en/series_soft-faced_hammers_101.html

Series Soft-Faced Hammers



Wide range of applications



They come in soft, medium and hard designs for a wide range of applications from universal use to splinter-free applications on sharpedged work pieces.

High quality ash wood



Powerful work is ensured with handles out of high quality ash wood.

Colour guidance system



Colour

systemsystemsystemli>YellowRepair/maintenanceli>RedSuitable for hammering sharpedged work pieces; bodyshops, automotive, engineeringli>Vii>Vii>IISuitable for metal processing and removal of dents; tent, large building and exhibition stand construction

guidance

Secure



The double-sided conical design creates an unbreakable and secure link between the handle and head of the hammer.

Versatile



Versatile use thanks to the soft faced heads that can be retrospectively fitted.

101 Soft-faced hammer with nylon head sections, # 3 x 33 mm

Series Soft-Faced Hammers



Further versions in this product family:

				\(\rangle \)
	#	mm	mm	mm
050003050011)	1	23.0	76.0	250.0
05000310001 ¹⁾	2	28.0	87.0	265.0
05000315001 ¹⁾	3	33.0	96.0	280.0
05000320001 ¹⁾	4	36.0	102.0	290.0
05000325001 ¹⁾	5	41.0	108.0	320.0
050003300011)	6	51.0	117.0	340.0
050003350011)	7	61.0	131.0	380.0

¹⁾ This item will be discontinued from 28 February 2025.