#### **Series Soft-Faced Hammers**





**EAN:** 4013288001382 **Size:** 290x105x35 mm

Part number:05000320001Weight:471 gArticle number:101Country of origin:CZ

Customs tariff 82052000

number:

- Powerful hammering with surface protection
- Soft-face hammers with hammer head out of nylon
- Suitable for sheet metal and renovation work as well as for tent, hall and fair booth construction jobs
- Inseparable and secure connection between the hammer handle and head
- High-quality ashwood handle

Wera soft-face hammers. Double-sided conical design for a secure, inseparable connection between the hammer handle and head. The hammer head is made out of nylon; the handle out of high quality ash wood. Diverse applications thanks to the interchangeable soft-face hammer heads. Suitable for sheet metal and renovation work as well as for tent, hall and fair booth construction jobs.

Web link https://products.wera.de/en/series\_soft-faced\_hammers\_101.html

### **Series Soft-Faced Hammers**



## Wide range of applications




They come in soft, medium and hard designs for a wide range of applications from universal use to splinter-free applications on sharpedged work pieces.

## High quality ash wood



Powerful work is ensured with handles out of high quality ash wood.

## Colour guidance system



systemsystemsystemli>YellowRepair/maintenanceli>RedSuitable for hammering sharpedged work pieces; bodyshops, automotive, engineeringli>Vii>Vii>IISuitable for metal processing and removal of dents; tent, large building and exhibition stand construction

#### Secure



The double-sided conical design creates an unbreakable and secure link between the handle and head of the hammer.

### Versatile



Versatile use thanks to the soft faced heads that can be retrospectively fitted.

05000320001 - 4013288001382

# 101 Soft-faced hammer with nylon head sections, # 4 x 36 mm

## **Series Soft-Faced Hammers**



## Further versions in this product family:

				<b>A</b>
	#	mm	mm	mm
050003050011)	1	23.0	76.0	250.0
05000310001 <sup>1)</sup>	2	28.0	87.0	265.0
05000315001 <sup>1)</sup>	3	33.0	96.0	280.0
05000320001 <sup>1)</sup>	4	36.0	102.0	290.0
05000325001 <sup>1)</sup>	5	41.0	108.0	320.0
050003300011)	6	51.0	117.0	340.0
050003350011)	7	61.0	131.0	380.0

<sup>1)</sup> This item will be discontinued from 28 February 2025.