


160 iS/7 Rack Screwdriver set Kraftform Plus Series 100, single-pole phase tester and rack. With reduced blade diameter, 7 pieces
Kraftform Plus – Series 100 VDE



| | | | |
|------------------------|---------------|-------------------------------|---------------|
| EAN: | 4013288160713 | Size: | 285x210x55 mm |
| Part number: | 05006480001 | Weight: | 653 g |
| Article number: | 160 iS/7 | Country of origin: | CZ |
| | | Customs tariff number: | 82054000 |

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Reduced shaft diameter

7-piece screwdriver set with reduced shaft diameter and integrated insulation protection so that even low-lying screw and spring elements can be accessed and actuated. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Take it easy Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace. Including single-pole phase tester and 1 rack for storage.

Web link
https://products.wera.de/en/screwdrivers_kraftform_plus_series_100_vde_160_is_7.html

Wera - 160 iS/7
05006480001 - 4013288160713

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de


160 iS/7 Rack Screwdriver set Kraftform Plus Series 100, single-pole phase tester and rack. With reduced blade diameter, 7 pieces
Kraftform Plus – Series 100 VDE



VDE-insulated screwdriver with reduced blade diameter



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

PlusMinus screwdrivers



For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Individually tested



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle




Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Take it easy Tool Finder



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_100_vde_160_is_7.html

Wera - 160 iS/7

05006480001 - 4013288160713

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

160 iS/7 Rack Screwdriver set Kraftform Plus Series 100, single-pole phase tester and rack. With reduced blade diameter, 7 pieces
Kraftform Plus – Series 100 VDE



Set contents:

162 iS PH VDE Insulated screwdriver with reduced blade diameter for Phillips screws, PH 1 x 80 mm



| | | |
|-------------|----|---------------|
| 05006450001 | 1x | PH 1 x 80 mm |
| 05006451001 | 1x | PH 2 x 100 mm |



165 iS PZ/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Pozidriv/slotted), # 2 x 100 mm



| | | |
|-------------|----|--------------|
| 05006466001 | 1x | # 2 x 100 mm |
|-------------|----|--------------|



160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 0.6 x 3.5 x 100 mm



| | | |
|-------------|----|--------------------|
| 05006440001 | 1x | 0.6 x 3.5 x 100 mm |
| 05006441001 | 1x | 0.8 x 4 x 100 mm |
| 05006442001 | 1x | 1 x 5.5 x 125 mm |



247 Single-pole phase tester, 0.5 x 3 x 70 mm



| | | |
|---------------------------|----|-----------------|
| 05005655001 ¹⁾ | 1x | 0.5 x 3 x 70 mm |
|---------------------------|----|-----------------|

¹⁾ Product not available in the USA and Canada.



Product not available in the USA and Canada.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_100_vde_160_is_7.html

Wera - 160 iS/7
05006480001 - 4013288160713

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de