

6000 Joker Ratcheting combination wrenches, Imperial, 7/16" x 165 mm

6000 Joker Ratcheting combination wrenches



EAN:	4013288167378	Size:	245x50x22 mm
Part number:	05073282001	Weight:	97 g
Article number:	6000 Joker Imperial	Country of origin:	CZ
		Customs tariff number:	82041100

- Practical holding function thanks to the metal plate in the jaw
- Limit stop prevents any slipping
- The double-hex geometry reduces the risk of slipping
- Return angle of only 30°
- With Take it easy tool finder: colour coding by size

High quality, imperial, combination ratchet wrench by Wera. Everything that a wrench has to be able to do. And a whole lot more. Faster, better, stylish. Yes, a real Joker. The new generation of combination ratchet wrenches. Suitable for hexagon socket screws, bolts or nuts. Comes with holding function, thanks to the metal plate in the jaw, which reduces the risk of dropping nuts and bolts. The replaceable metal plate in the jaw secures nuts and bolts with its extra hard teeth and reduces the danger of slipping. The integrated limit stop prevents any slipping around the bolt head and allows higher torque to be applied. The double-hex geometry makes for a positive connection with nuts or bolts and reduces the risk of slipping. A return angle of only 30° at the open end prevents any time consuming flipping of the wrench. The ratchet mechanism at the ring end, with an exceptional, fine-tooth mechanism - 80 teeth in all - enables flexibility even in very confined working spaces. The specially forged geometry ensures high torque transfer and strength. The ratchet is manufactured out of high performance chrome molybdenum steel with nickel-chrome coating for high corrosion protection. "Take it easy" Tool Finder with colour coding according to sizes.



HOLDING
FUNCTION



LIMIT
STOP



ANTI-SLIP



SMALL
ANGLE



TAKE IT EASY
TOOL FINDER

Web link

https://products.wera.de/en/joker_6000_joker_ratcheting_combination_wrenches_6000_joker_imperial.html

Wera - 6000 Joker Imperial
05073282001 - 4013288167378

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

6000 Joker Ratcheting combination wrenches

Joker open-ended wrench




When we began to think about open-ended wrenches, we asked ourselves: why does the wrench always have to be flipped over; why does it have an offset design; why does it slip off injuring fingers? The new design of the open end resulted in a real "Joker" that works even when all other trumps have been played.

Ring ratchet spanner Joker 6000



The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately - no additional tools required.

Integrated limit-stop



Constant re-positioning of the wrench? Difficulty holding fasteners in confined spaces? Easing off to avoid any risks of injury or fastener damage? That was yesterday. Today, the Joker prevents slipping off of the fastener head with its integrated limit-stop - no longer is the thumb needed to act as a depth stop. This makes applications much easier and allows significantly more force to be applied during fastening jobs.

Double-hex geometry



The Joker's clever double-hex geometry delivers a very positive connection with nuts or bolts - it's a perfect fit. And the exchangeable, hardened metal gripping plate in the Joker's open end literally bites itself into the bolt, with its extremely hard tips. Both features combine to prevent slipping, even at higher torque.

Web link


https://products.wera.de/en/joker_6000_joker_ratcheting_combination_wrenches_6000_joker_imperial.html

Wera - 6000 Joker Imperial
05073282001 - 4013288167378

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

6000 Joker Ratcheting combination wrenches

Small return angle



Instead of 60°, the Joker only has a 30° back-pivoting angle thanks to its unique double-hex design. Along with the Joker's straight neck, this means that flipping the wrench has become a thing of the past. With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional tools fail. Particularly in confined spaces, where conventional open-jawed wrenches cannot be used. The combination of limit stop and small return angle enables effective work, even on screw pipe connections.

Fine tooth mechanism



The ratcheting feature at the ring end boasts an exceptional, fine tooth mechanism - 80 teeth in all - which provides greater flexibility, even in very confined workspaces.

"Take it easy" tool finder



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Further versions in this product family:



inch



mm



mm



mm



mm



mm

		inch	mm	mm	mm	mm	mm
05073280001	blau_307C	5/16"	144	20	5.5	18	7
05073281001	rot_200C	3/8"	159	22	5.5	21	7.2
05073282001	violett_2735C	7/16"	165.0	25	6.3	22	7.5
05073283001	tuerkis_339C	1/2"	177	27.3	7	25	8.6
05073284001	pink_241C	9/16"	188	29.3	7.5	28	9.2
05073285001	schwarz_blackC	5/8"	212	35	8.2	32.7	10.5
05073286001	cyan_2985C	11/16"	235	39	9	33.8	11
05073287001	gelb_123C	3/4"	246	42	9.5	34.8	11

Web link

https://products.wera.de/en/joker_6000_joker_ratcheting_combination_wrenches_6000_joker_imperial.html

Wera - 6000 Joker Imperial
05073282001 - 4013288167378

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de