

Series 7400 Kraftform adjustable torque screwdrivers (2.5-29.0 in. lbs.) with Rapidaptor quick-release chuck, 7445 x 2.5-11.5 in. lbs.  
Series 7400 Kraftform Torque Screwdrivers - Variable torque adjustment models



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288102881 | <b>Size:</b>                  | 155x37x37 mm |
| <b>Part number:</b>    | 05074710001   | <b>Weight:</b>                | 177 g        |
| <b>Article number:</b> | 7400 inch     | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82041100     |

- Adjustable Kraftform torque screwdriver with Rapidaptor quick-release chuck
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached
- Numerical torque value indicator

Wera torque screwdriver. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).



**Web link**

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_variable\\_torque\\_adjustment\\_models\\_7400\\_inch.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_inch.html)

Wera - 7400 inch  
05074710001 - 4013288102881

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Adjustable Torque Screwdrivers**



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

**Simple setting**



Simple setting of the required torque by hand.

**Easy-to-read**



Easy-to-read scale value.

**Attachable magnifying glass**



Articles 7430, 7431 and 7432 all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

**Measurement accuracy**



Measurement accuracy is  $\pm 6\%$  (article 1430:  $\pm 10\%$ ) in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

**Unlimited torque**









Unlimited torque for loosening seized screws.

**Versatile**



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

**Further versions in this product family:**

|  |                    |  |  |  |  |  |  |          |
|--|--------------------|---|---|---|---|---|---|----------|
|  | art. no.           | inch  | in. lbs.  | in. lbs.  | mm  | mm  | inch  |          |
|  | <b>05074710001</b> | <b>7445</b>   | <b>1/4</b>  | <b>2.5-11.5</b>   | <b>0.5</b>  | <b>105</b>  | <b>155</b>  | <b>6</b> |
|  | 05074711001        | 7446  | 1/4   | 11.0-29.0   | 1.0   | 105   | 155   | 6        |

**Web link**

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_krafftform\\_torque\\_screwdrivers\\_variable\\_torque\\_adjustment\\_models\\_7400\\_inch.html](https://products.wera.de/en/torque_tools_series_7400_krafftform_torque_screwdrivers_variable_torque_adjustment_models_7400_inch.html)

Wera - 7400 inch

05074710001 - 4013288102881

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)