


1430 ESD Kraftform Micro adjustable torque screwdrivers (0.02-0.11 Nm) with quick-release chuck, 1430 ESD x 0.02-0.06 Nm
Series 7400 ESD Kraftform Torque Screwdrivers



EAN:	4013288179043	Size:	145x23x23 mm
Part number:	05074802001	Weight:	41 g
Article number:	1430 ESD	Country of origin:	CZ
		Customs tariff number:	82054000

- Adjustable Kraftform Micro ESD torque screwdriver with quick-release chuck
- ESD-safe tool thanks to surface resistance of $\leq 10^9$ Ohm
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Suitable for bits with 4 mm halfmoon and 4 mm HIOS drive
- Applications e.g. on smartphones, mobile phones, cameras, electronic equipment

Torque tool with adjustable torque of 2.0 to 6.0 cNm (accuracy +/- 10%). Compact handle/interchangeable blade system for torque controlled precision screwdriving. The Kraftform Micro ESD torque screwdriver is ideal for torque controlled jobs on electrostatically-susceptible components. Suitable for the take-up of bits with 4 mm halfmoon drive (Wera series 9) and 4 mm HIOS drive (Wera series 21). Tamperproof. Distinct audible and perceivable excess load signal when the pre-set torque value is reached. Unlimited manual loosening torque. Electrical surface resistance of $\leq 10^9$ Ohm for secure protection against electrostatic charge. Manufactured in accordance with DIN EN 61340-5-1. Handle/Interchangeable blade system for rapid blade change. Kraftform Micro handle with twist cap and free-turning zone for rapid twisting, making any time-consuming repositioning of the fingers unnecessary. Power zone with integrated soft zones for the transfer of higher tightening and loosening torque. Precision zone directly above the blade for the right angle for adjustment work. Rapid fixing of the bit: just push the bit into the insert for automatic locking and a secure fit. To change the bit, simply push the sleeve forward and remove. Free-turning sleeve for simple guidance of the tool during the screwdriving process. Bits suitable for manual as well as power tool operations with electric screwdrivers (e.g. HIOS, Delvo, Sehan). Applications for example on smartphones, cell phones, cameras, electrical appliances, in dental labs and dental surgeries.



Web link

https://products.wera.de/en/torque_tools_series_7400_esd_kraftform_torque_screwdrivers_1430_esd.html

Wera - 1430 ESD
05074802001 - 4013288179043

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

1430 ESD Kraftform Micro adjustable torque screwdrivers (0.02-0.11 Nm) with quick-release chuck, 1430 ESD x 0.02-0.06 Nm Series 7400 ESD Kraftform Torque Screwdrivers




Adjustable torque screwdrivers

Wera ESD Tools

High protection

For Halfmoon and HIOS Bits



They can be adjusted by hand to the corresponding scale value. Also available in ESD version (also with take-up for HIOS/Halfmoon bits) and with Kraftform Micro handle.

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.


Features a combination bitholder for both bits with Halfmoon and bits with HIOS drive.

Adjustable Torque Screwdrivers

Attachable magnifying glass

The fast-turning zone

The power zone



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

Articles 1430 ESD and 1431 ESD, all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

The fast-turning zone just below the rotating cap allows rapid twisting.

The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

Web link

https://products.wera.de/en/torque_tools_series_7400_esd_kraftform_torque_screwdrivers_1430_esd.html





Wera - 1430 ESD
05074802001 - 4013288179043

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

1430 ESD Kraftform Micro adjustable torque screwdrivers (0.02-0.11 Nm) with quick-release chuck, 1430 ESD x 0.02-0.06 Nm
Series 7400 ESD Kraftform Torque Screwdrivers



Further versions in this product family:

	art. no.	 Nm	 Nm	 mm	 inch	
	05074802001¹⁾	1430 ESD	0.02-0.06	0.0025	141	5 7/16"
	05074804001 ¹⁾	1431 ESD	0.05-0.11	0.005	141	5 7/16"

1) With attachable magnifying glass, dramatically improving visibility.

Web link

https://products.wera.de/en/torque_tools_series_7400_esd_kraftform_torque_screwdrivers_1430_esd.html

Wera - 1430 ESD
05074802001 - 4013288179043

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de