

## TECHNICAL DATA SHEET

# SECUMAX POLYCUT MDP NO. 8500772

## Safety technology



Concealed blade – a maximum degree of safety

The SECUMAX POLYCUT MDP blade is not an open one, but is hidden from people and goods. This provides you with the highest degree of safety from cut injuries and from damage to goods.



#### DISPOSABLE SAFETY KNIFE WITH CONCEALED BLADE, ESPECIALLY FOR CUTTING FOIL AND PAPER.

**Order No.** 8500772.12

### The all-rounder among specialists. Metal detectable.

The SECUMAX POLYCUT MDP is another of our small, plastic disposable knives and is special by being an all-rounder. The larger gap between the blade and plastic means it can cut through multiple layers of material. Furthermore, with its long pointed nose you are able to cut through paper film, etc. Your company will be especially pleased that it is also made of plastic that can be traced by a metal detector and can therefore be found again.

## Metal detectable

A cutting tool, or parts of it, can get lost while working. But only for a short while. Thanks to its ability to be detected by a metal detector you can find it again, before it leaves the company with your goods.

#### It's all protected

The stainless steel quality blade is safely embedded between the nose and the handle. So it only cuts what you really want to cut. And there is no risk to your goods while doing so.

## Singularly good


The SECUMAX POLYCUT MDP is a disposable safety knife. Since you do not have to change the blade, neither you nor your staff can come into contact with it. An additional benefit as far as safety is concerned.

### Long, pointed nose

Why the extra long and pointed nose in the SECUMAX POLY-CUT MDP? Because you can place it particularly well in the spaces in between. The cutting material is also led to the blade in a much more reliable way.

#### Ideally placed

You won't misplace the SECUMAX POLYCUT MDP so easily. The safety knife is equipped with an eyelet so it can be kept in an easy to find place.



## PRODUCT FEATURES

#### Technical features



Maximum safety



Metal detectable



X-ray detectable



Disposable knife



Ergonomic



Cutting depth



For right and left handers



Lanyard hole



Stainless



Abrasion resistant



Printable for promotional purposes

## Main cutting materials



Wrapping, stretch and shrink foil



Tape



Layers of foil or paper



Yarn, cord



Envelope

Installed blade

Blade thickness 0.30 mm.

## BLADE CHANGE

The stainless steel blade is moulded into the body of the knife and cannot be changed.



Training video



Technical data sheet



Consulting service

#### PRODUCT AND PACKAGING DETAILS

Order No.	NO. 08500772.12	Packaging unit (PU)	10 in box (loose)
Knife size (L x W x H)	76.1 x 3 x 45.1 mm	Size (PU)	83 x 35 x 47 mm
Weight knife	9.4 g	Weight (PU)	104.2 g
Basic material	Metal detectable plastic	EAN Code (PU)	4002632801235
Cutting depth	3.0 mm	Quantity in outer pack	-
		Customs tariff number	82141000

#### SAFETY CERTIFICATE

Date of issue	23.10.2018	
Certification	GS certificate NO. 603847-6480-55094-2018	

Certificates and awards



#### **SECURITY ADVICE**

To ensure that you use your new MARTOR knife safely and most effectively, please read and note the following user-instructions. Please keep the written guide in a safe place so that you can access it at any time.

- **1. General application instructions:** Please always use the product carefully for manual cutting work only and not for any purposes other than those that are intended. Please take the correct handling and the proper use of the knives into account in this regard. As an additional safety measure, we recommend the wearing of safe gloves.
- 2. Special application Instructions to avoid the danger of injuries: Only use cutting tools that are in perfect condition and have sharp, clean and undamaged MARTOR blades. Employ the utmost care when handling the knives. Prior to use, familiarise yourself with the safety features and their functioning. Ensure that these safety features are not impaired by the type of material to be cut. CAUTION: The blade is sharp and can result in serious and deep cuts. Therefore, never reach into the blade! Do not place your free hand in the line of cutting and never cut directly towards you.
- **3. Replacement of spare parts:** This knife is a disposable product. It is not designed to have its blades changed or any other of its components replaced. If the knife shows signs of aging or any other wear, e.g. which impair the safety features or usage, the knife must be taken out of service and replaced. Do not modify this product in any way. Modifications of any kind may impair product safety. CAUTION: The risk of injury caused by manipulation of this product is extremely high.
- **4. Non-use of the knife:** Always secure the blade in such a way (depending on product type) that injuries due to cuts are excluded. Store the knife in a secure place.
- **5. Care instructions:** To guarantee a long service life, always keep the knife clean and do not expose it to unnecessary soiling and humidity.

CAUTION: No liability will be assumed for consequential losses. Subject to technical changes and errors! This knife does not belong in the hands of children! MDP TEST CARD SET NO. 9910



There are five cards with different plastic balls in the MDP TEST CARD SET – between 2.5 mm and 8 mm in size. You can reliably test the effectiveness of your metal detectors using the "visiting card".

## MANUFACTURER