

Product Datasheet LED head torch 9790.028 KS-7630 MCII



UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189, D-90766 Fürth

Product features

- Compact design
- Three different operating modes
- Protection level: IP 67 (dust- and waterproof)
- Operating temperature: -15 °C to + 60° C
- Power supply: Lithium-ion battery
- Luminous flux: up to max. 230 lumen
- Light duration: 30 hours
- Charging time: approx. 9 hours
- >80% capacity after 500 cycles
- ATEX permission (compliance 2014/34/EU)

Weight	145 g
Delivery	LED head torch, charger

Versions

Article number	Colour/Version	Retail unit
9790.028	LED head torch KS-7630 MCII	1 piece