


Product Datasheet model uvex x-fit 9199 277

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• Functional and sporty Design• Perfect closed fitting• X-shaped soft nose design for stability and protection• High-performance uvex supravision coating• Temple as duo-component equipment-rail for functional add-ons:<ul style="list-style-type: none">- easy adaptable and adjustable headband (item. no. 9958 023) for a secure fitting- uvex LED mini light for additional lightning (item no. 9999 100)
Technical details	
Frame	
Material	Temples ABS
Colour	anthracite, light grey

Model No.	Marking 9199
Manufacturer's ID code	W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
Lens	
Material	PC (Lens) TPE (x-Nose)
Thickness	1,9 mm at PD
Coating	uvex supravision excellence
Colour	grey 23% (Lens) anthracite (x-Nose)
UV protection	UV400
Marking	
Filter	5-2,5 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight	24 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II