


**Product Datasheet model uvex x-fit 9199 247**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

<b>Product characteristics</b>	<ul style="list-style-type: none"><li>• Functional and sporty Design</li><li>• Perfect closed fitting</li><li>• X-shaped soft nose design for stability and protection</li><li>• High-performance uvex supravision coating</li><li>• Temple as duo-component equipment-rail for functional add-ons:<ul style="list-style-type: none"><li>- easy adaptable and adjustable headband (item. no. 9958 023) for a secure fitting</li><li>- uvex LED mini light for additional lightning (item no. 9999 100)</li></ul></li></ul>
<b>Technical details</b>  <b>Frame</b>  Material Colour	<b>Temples</b> ABS blue, anthracite

Model No.	<b>Marking</b> 9199
Manufacturer's ID code	W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
<b>Lens</b>	
Material	PC (Lens) TPE (x-nose)
Thickness	1,9 mm at PD
Coating	uvex supravision excellence
Colour	clear (Lens) anthracite (x-nose)
UV protection	UV400
<b>Marking</b>	
Filter	2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

**Miscellaneous**

Weight	24 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II