

Product data sheet for uvex phynomic pro 2



MADE IN GERMANY 

Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
 Elso-Klöver-Str. 6
 D-21337 Lüneburg
 uvex-safety.de

The uvex phynomic pro 2 is a sensitive safety glove for assembly activities in slightly damp/oily areas. The flexible, non-slip aqua-polymer pro coating has outstanding dirt- and moisture-repellent properties, allowing for excellent grip. The safety glove is also impermeable to resins or highly viscous pastes, while still remaining breathable. The bamboo-polyamide-elastane liner feels extremely comfortable on your skin thanks to bamboo viscose. After all, this natural fibre provides high breathability and excellent moisture absorption. The uvex phynomic pro 2 is free from accelerators and offers dermatologically tested (proDERM) skin compatibility, making it ideal for allergy sufferers as well as a solvent-free alternative for PU-glove users.

Characteristics

- Good grip
- Extremely flexible

Suitability for industrial work environments

- Suitable for damp and oily work environments
- Suitable for dry work environments

Material number	60064
Sizes	5 - 12
Standard	ISO 21420:2020, EN 388:2016 + A1:2018
Performance class in accordance with EN 388	2 1 2 1 X
Outer material	polyamide (PA), Elastane, Bamboo viscose
Coating	Aqua-polymer Pro
Coating surface area	Fingertips, Palm
Type	With knitted cuff
Colour	Blue, Grey