

MACCROSSROAD 3.0 S3 HIGH META / 67353 / EN 20345:2011 - S3 M CI HI HRO SRC //
High safety shoes

- D30® metatarsal protection (M)
- multipurpose
- slip-resistant
- cushioned
- HRO
- comfortable
- flexible
- durable
- 100% metal-free
- **sizes:** 36 - 48


**100%
metal
free**

APPLICATIONS //

utilities | construction | civil engineering | oil & gas | heavy industry | rail | ports | defense | agriculture & green spaces

TECHNICAL SPECIFICATIONS //

- **sole:** MACSOLE® ADVENTURE 3.0 rubber with MACABSORB EVA insert in forefoot & heel for excellent shock absorption and flexibility | excellent levels of grip (SRC) | oil, hydrocarbon & chemical-resistant | resistance to contact heat up to 300°C (HRO) | ergonomic sole supports natural rolling movement of the foot | all-terrain sole profile disperses surface debris for better grip | rubber scuff cap protects leather prolonging product life
- **upper:** water-resistant full-grain leather | Agile Ankle Guard & reinforced heel supports foot for better stability especially on uneven surfaces while retaining a high level of movement
- **lining:** 3D mesh for better ventilation & fast drying
- **tongue:** gusset tongue made with synthetic & water-resistant textile to keep dirt and liquid out | very flexible 100 J metatarsal protection integrated within the tongue | loop holds tongue in place
- **ankle padding:** flexible & compact foam around ankle and Achilles tendon for protection and comfort
- **toe cap:** metal-free | lighter than steel | does not conduct heat & cold compared to metal toe cap
- **penetration-resistant midsole:** metal-free | light & flexible | does not conduct heat & cold compared to a metal sole | protects 100% of the surface of the foot
- **insole:** removable | anatomically shaped with shock absorbers in the heel & forefoot | microfibre top layer for better abrasion resistance & durability, very high moisture absorption capacity and fast drying | bottom layer made from 85% recycled open cell PU foam | washable at 30°C enhances hygiene
- **sizing system:** French (EU) | width 11
- **weight:** 740 g in size 42