


**Product Datasheet model winner 9159 118**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

<b>Product characteristics</b>	<ul style="list-style-type: none"><li>• edgeless, metal-framed spectacles with sprung side arms</li><li>• optimum eye coverage</li><li>• anatomically adjustable, soft nose pads</li></ul>
<b>Technical details</b>	
<b>Frame</b>	
Material	<b>Front piece</b> Metal
Colour	gun
Material	<b>Side piece</b> Metal
Colour	gun
Material	<b>Temple</b> Rubber
Colour	black

Manufacturer's ID code	<b>Marking</b> W
Applicable EN norm	166
Low-energy impact	F (45 m/s)
Conformity symbol	CE
<b>Lens</b>	
Material	PC
Thickness	2,2 mm
Coating	scratch resistant, non-fogging
Colour	grey
UV protection	UV 400
<b>Filter</b>	
Filter	5-2,5 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Low-energy impact	F (45 m/s)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
<b>Miscellaneous</b>	
Weight	29 g
Packing	5 spectacles per box 150 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II