

uvex

**SAFETY
EYEWEAR**

27.05.2021

Product Datasheet model uvex i-vo 9160 520



**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics


- fashionable safety spectacles with adjustable side arms
- reliable protection provided by its perfect fit: multi-level side arm inclination and different side arm lengths allow the wearer to adjust the spectacles to suit their own face shape
- soft, uvex quattroflex arms and soft components at the nose and forehead ensure a comfortable, pressure-free fit
- the shape of the lenses ensures unrestricted peripheral vision

Technical details

Frame

Material
Colour

Front piece
TPU/TPE
blue, orange

Material	Side piece
Features	PA
Colour	5 position length adjustability blue
Material	Temple
Features	PBT+PC/TPE
Colour	quattroflex temple blue, orange
Manufacturer's ID code	Marking
Applicable EN norm	W
Low-energy impact	166
Resistance to high speed particles at extremes of temperat.	F (45 m/s) T
Lens	
Material	PC
Thickness	3 mm at PD
Coating	uvex supravision sapphire
Colour	amber
UV protection	UV400
Filter	Marking
Manufacturer's ID code	2C-1,2 (DIN EN 170)
Optical class	W
Low-energy impact	1
Resistance to high speed particles at extremes of temperat.	F (45 m/s) T
Surface resistance to fine particles	K
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight

33 g

Packing

5 spectacles per box

200 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 170

PPE Category

Category II