

Product Datasheet origin 8450.2 S3 HI CI HRO SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

Product information	<ul style="list-style-type: none">• Sturdy shoe suitable for general use• Extra wide fit• Water-resistant nappa leather• Dust tongue• Breathable textile lining• uvex 3D hydroflex® foam insole for exceptional shock absorption in the heel and under the forefoot• HRO symbol for heat-resistant outsole for brief exposure up to +300 °C• HI symbol for heat-insulating sole• CI symbol for cold-insulating sole• Steel toe cap and midsole
Outsole	<ul style="list-style-type: none">• Dual sole made from uvex softcell midsole material for excellent shock absorption and comfort underfoot, and uvex ultragrip outsole made from newly developed rubber blend• Uvex ultragrip outsole is shaped like a shell, almost encloses the softcell midsole• Outsole is temperature-resistant from -20°C to +300°C• Suitable for general use on almost all surfaces• Resistant to most chemicals• Excellent slip prevention, even on damp and oily surfaces• Silicone-free• Extremely cut-resistant• Very low abrasion

	<ul style="list-style-type: none"> • Antistatic • Self-cleaning tread
Technical data	Art.-no. 8450.2 Width 11,5 Standard EN ISO 20345:2011 S3 HI CI HRO SRC Size 38 – 48
Accessories	<p><i>ultra comfortable uvex 3D hydroflex® foam climatic insole</i> (article no.: 9595.4)</p> <ul style="list-style-type: none"> • Additional shock-absorbing elements in the heel and under the front of the foot ensure comfort in high-pressure zones and provide the foot with “full-surface” shock absorption • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure • Antistatic system • Supports the foot arch <p><i>Laces</i></p> <ul style="list-style-type: none"> • Black (article no.: 9599.9 09)