

Product Datasheet uvex 9780 antistatic and antistatic-WR



UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189, D-90766 Fürth

Product characteristics	<ul style="list-style-type: none">• side Euroslots (30 mm)• three variable air vents for maximum ventilation• conventional suspension harness for a comfortable fit (antistatic)• suspension harness with wheel ratchet for individual width adjustment (antistatic-WR)• 6-point textile suspension harness ensures an optimum fit and comfort• large printing areas for individualization available
Material	PP
Weight	9780 antistatic: 380 g 9790 antistatic-WR: 430 g
Standard	EN 397 + ATEX Directive 94/9/EG
Size range	9780 antistatic: 51-61 cm 9780 antistatic-WR: 52-61 cm
Retail unit	25 pieces

uvex 9780 antistatic with conventional suspension harness

Art. no.	Typ	color
9780.020	uvex 9780, long brim	white

uvex 9780 antistatic-WR with wheel ratchet system

Art. no.	Typ	color
9754.000	uvex 9780, long brim	white
9754.100	uvex 9780, long brim	sky-blue

accessoires

Art. no.	Typ
9790.000	Suspension harness
9760.005	Sweatband
9790.035	Leather Chinstrap
9790.021	Forked chinstrap (not for use in explosive atmospheres zone 0)
9790.077	Helmet slot plugs set
9790.006	Paper caps

Head torches

Art. no.	Typ
9790.058	LED head torch KS-7610-MX
9790.038	LED head torch KS-7810-MX (ATEX)
9790.063	LED head torch pheos LED Lights ATEX