

Product Datasheet uvex 2 xenova 9554.7 - .9 S1 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

General features	<ul style="list-style-type: none">• Low weight and modern perforated S1 safety shoe• Upper: microvelour• Suitable for people allergic to chrome as it's made from synthetic materials• All sole materials are free of silicones, plasticisers and other paint wetting impairment substances
Protection features	<ul style="list-style-type: none">• Meets ESD requirements: resistance to ground < 35 megaohm• 100% metal-free uvex xenova® toe cap. Compact design, anatomical shape, good lateral stability, no thermal conductivity properties• Ergonomically designed outsole made from dual density polyurethane with excellent slip resistance
Comfort features	<ul style="list-style-type: none">• Light weight and optimised shock absorption• Outstanding wearer comfort results from a newly developed last and climate-optimised, breathable materials• Removable comfort insole, antistatic, with moisture control system and additional shock absorption in the heel and at the front of the foot• Soft padding on collar
Outsole	<ul style="list-style-type: none">• PUR outsole, non-marking• Ergonomically designed tread• Extremely flexible, excellent shock absorption• Unique PUR outsole system makes the shoe ultra-light• Two-layer system with abrasion-resistant and cut-resistant outsole• Excellent slip resistance• Self-cleaning tread

	<ul style="list-style-type: none"> • Resistant to oil and petrol • Resistant to temperatures for short periods up to ca. +120°C 																
Certificates	<ul style="list-style-type: none"> • Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions. 																
Areas of application	<ul style="list-style-type: none"> • Moderate applications 																
Technical data	<table> <tr> <td>Art.-no.</td> <td>9554.7</td> <td>.8</td> <td>.9</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S1 SRC</td> </tr> <tr> <td>Size</td> <td colspan="3">38 – 52</td> </tr> </table>	Art.-no.	9554.7	.8	.9	Width	10	11	12	Standard	EN ISO 20345:2011 S1 SRC			Size	38 – 52		
Art.-no.	9554.7	.8	.9														
Width	10	11	12														
Standard	EN ISO 20345:2011 S1 SRC																
Size	38 – 52																
Accessories	<p><i>comfortable climatic insole</i> (Article-no.: 9534.7-9)</p> <ul style="list-style-type: none"> • Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure <p><i>Shoe laces</i></p> <ul style="list-style-type: none"> • black (Article-no.: 9599.9 09) 																