

Product data sheet for uvex profapren



EN ISO 374-1:2016 / Type A



AKLMNO

EN 388:2016



3 1 3 1 X

Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
 Elso-Klöver-Str. 6
 D-21337 Lüneburg
 uvex-safety.de

The chloroprene chemical protection glove with flocked cotton liner protects wearers against many mechanical and chemical risks. It is perfectly suited to precision work in the chemical industry, but also for cleaning work, in the metal processing industry, for example.

Characteristics

- Good grip, even in wet work environments
- Good fit

Material number	60119
Sizes	7 - 11
Standard	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016
Test chemicals	Methanol (A), Sodium hydroxide 40% (K), Sulphuric acid 96% (L), Nitric acid 65% (M), Acetic acid 99% (N), Ammonia water 25% (O)
Performance class in accordance with EN 388	3 1 3 1 X
Outer material	Cotton-flocked
Coating	Polychloroprene
Coating surface area	Fully coated
Coating thickness	0.75 mm
Type	With gauntlet
Colour	Blue, Dark blue