

Product data sheet for uvex profastrong NF33



Thanks to its good resistance, the popular uvex profastrong NF33 chemical protection glove really shines when it comes to handling harmful oils, grease and liquids.

Characteristics

- Good grip, even in wet work environments
- Good mechanical abrasion resistance
- Good fit

Material number	60122
Sizes	7 - 11
Standard	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016, EN ISO 374-5:2016
Test chemicals	Methanol (A), n-Heptane (J), Sodium hydroxide 40% (K), Sulphuric acid 96% (L), Ammonia water 25% (O), Formaldehyde 37% (T)
Performance class in accordance with EN 388	4 1 0 1 X
Outer material	Cotton-flocked
Coating	Nitrile rubber (NBR)
Coating surface area	Fully coated
Coating thickness	0.38 mm
Type	With gauntlet
Colour	Green
Glove length	33 cm

EN ISO 374-1:2016 / Type A



AJKLOT

EN ISO 374-5:2016



EN 388:2016



4 1 0 1 X



Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
 Elso-Klöver-Str. 6
 D-21337 Lüneburg
 uvex-safety.de