

## Product data sheet for uvex u-fit strong N2000



The uvex u-fit disposable safety glove excels thanks to its impressive mechanical resistance. It is flexible and robust, provides good protection against chemicals and splashes – and is perfect for cleaning work, laboratory work or the food industry.

### Characteristics

- Extremely flexible
- Very good tactile feel

**Material number** 60962

**Sizes** S - XXL

**Standard** EN 420:2003 + A1:2009,  
EN ISO 374-1:2016,  
EN ISO 374-5:2016

**Test chemicals** n-Heptane (J), Sodium hydroxide 40% (K), Sulphuric acid 96% (L), Ammonia water 25% (O), Hydrogen peroxide 30% (P), Hydrofluoric acid 40% (S), Formaldehyde 37% (T)

**Outer material** No lining

**Coating** Nitrile rubber (NBR)

**Coating surface area** Fully coated

**Coating thickness** 0.20 mm

**Type** With rolled edge

**Colour** Blue

EN ISO 374-1:2016 / Type A



JKLOPST

EN ISO 374-5:2016



### Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG  
Elso-Klöver-Str. 6  
D-21337 Lüneburg  
uvex-safety.de