

**Product Datasheet model i-3 s AR 9190 039**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

**Product  
characteristics**

- fashionable, 3-component safety spectacles with innovative features
- anti-reflective lenses provide protection against a transmission factor of > 96.5% to prevent distracting reflections
- small version of standard model uvex i-3
- metal-free
- reliable protection provided by its perfect fit: multi-level side arm inclination allows the wearer to adjust the spectacles to suit their own face shape
- soft, adjustable nose loops, soft, anti-slip sidearm pieces and metalfree hinged side arms (3-component technology) for high wearer comfort and to avoid pressure points

**Technical details****Frame**

Material  
Features  
Colour

Manufacturer's ID  
code  
Applicable EN norm  
Impact resistance  
Resistance to high  
speed particles at  
extremes of temp.  
Conformity symbol

**Lens**

Material  
Thickness  
Coating  
Colour  
UV protection

Filter  
Manufacturer's ID  
code  
Optical class  
Impact resistance  
Resistance to high  
speed particles at  
extremes of  
temperat.  
Conformity symbol  
Factory symbol

**Front piece/Temple**


TPU/TPE  
variable inclination, individually adjustable  
black, blue

**Marking**

W  
  
166  
F (45 m/s)  
T  
  
CE

PC  
2,2 mm  
uvex supravision AR  
clear  
UV 400

**Marking**

2C-1,2 (DIN EN 170)  
W  
  
1  
F (45 m/s)  
T  
  
CE  


**Miscellaneous**

Weight

30 g

Packing

5 spectacles per box

160 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 170

PPE Category

Category II