

Product Datasheet model i-3 9190 270

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

**Product
characteristics**

- fashionable, 3-component safety spectacles with innovative features
- 100% metal-free
- reliable protection provided by its perfect fit: multi-level side arm inclination allows the wearer to adjust the spectacles to suit their own face shape
- adjustable nose loops prevent complications caused by the spectacles slipping
- soft, adjustable nose loops, soft, anti-slip sidearm pieces and metalfree hinged side arms (3-component technology) for high wearer comfort and to avoid pressure points

Technical details**Frame**

Material
Features
Colour

Front piece/Temple

TPU/TPE
variable inclination, individually adjustable
anthracite-blue

Manufacturer's ID code
Applicable EN norm
Impact resistance
Resistance to high
speed particles at
extremes of temperat.
Conformity symbol

Marking

W
166
F (45 m/s)
T
CE


Lens

Material
Thickness
Coating
Colour
UV protection

PC
2,2 mm
uvex supravision sapphire
clear
UV 400

Filter
Manufacturer's ID code
Optical class
Impact resistance
Resistance to high
speed particles at
extremes of temp.
Surface resistance to
fine particles
Conformity symbol
Factory symbol

Marking

2C-1,2 (DIN EN 170)
W
1
F (45 m/s)
T
K
CE


Miscellaneous

Weight

30 g

Packing

5 spectacles per box

160 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 170

PPE Category

Category II