


**Product Datasheet model i-3 9190 880**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

**Product  
characteristics**

- fashionable, 3-component safety spectacles with innovative features
- uvex variomatic lenses accommodate fast in changing UV irradiation conditions by automatic darkening (10 s) and lightening (30 s)
- 100% metal-free
- reliable protection provided by its perfect fit: multi-level side arm inclination allows the wearer to adjust the spectacles to suit their own face shape
- adjustable nose loops prevent complications caused by the spectacles slipping
- soft, adjustable nose loops, soft, anti-slip sidearm pieces and metalfree hinged side arms (3-component technology) for high wearer comfort and to avoid pressure points
- Eye protection suitable for oil and gas applications

<b>Technical details</b>	
<b>Frame</b>	
Material	<b>Front piece/Temple</b> TPU/TPE
Features	variable inclination, individually adjustable
Colour	black-anthracite
	<b>Marking</b>
Manufacturer's ID code	W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperatures	T
Conformity symbol	CE
<b>Lens</b>	
Material	PC
Thickness	2,2 mm
Coating	uvex supravision variomatic
Colour	light green

	<b>Marking</b>
Filter	2-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperatures	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
<b>Miscellaneous</b>	
Weight	30 g
Packing	1 spectacle per box 42 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170