


Product Datasheet model i-3 9190 885

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

**Product
characteristics**

- fashionable, 3-component safety spectacles with innovative features
- 100% metal-free
- reliable protection provided by its perfect fit: multi-level side arm inclination allows the wearer to adjust the spectacles to suit their own face shape
- adjustable nose loops prevent complications caused by the spectacles slipping
- soft, adjustable nose loops, soft, anti-slip sidearm pieces and metalfree hinged side arms (3-component technology) for high wearer comfort and to avoid pressure points
- Eye protection suitable for oil and gas applications

Technical details	
Frame	Front piece/Temple
Material	TPU/TPE
Features	variable inclination, individually adjustable
Colour	black-light grey
	Marking
Manufacturer's ID code	W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,2 mm
Coating	Antifog on the inside
Colour	dark silvermirror
UV protection	UV 400
	Marking
Filter	5-3,1 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight	30g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II