

uvex

**SAFETY
EYEWEAR**

12.03.2019

Product Datasheet model uvex pheos guard 9192 181




**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics

- modern safety spectacles with a fashionable design and duo-spherical lens technology
- metal-free
- set consisting of fitted extra frame with soft padding and adapted headband
- additional eyebrow protection with Eye Plus Protection: a bevelled edge in upper area
- soft, non-slip ear pieces (uvex duo Component technology) prevent pressure points
- very large field of vision
- can be easily combined with other PPE
- suitable for the uvex helmet IES (Integrated Eyewear System)

Technical details	
Frame	
Material	Frame PBT+PC
Colour	black
Material	Foam Carrier PUR
Colour	black
Material	Temples POM/TPE
Colour	black-grey
Manufacturer's ID code	Marking W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,1 mm
Coating	supravisión extreme
Colour	grey
UV protection	UV 400

Filter	Marking 5-2,5 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Low-energy impact	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
Material	Headband synthetic headband
Features	adjustable
Colour	grey-black
Miscellaneous	
Weight	39 g
Packing	4 spectacles per box 128 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II