


Product Datasheet model uvex pheos 9192 280

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

**Product
characteristics**

- modern safety spectacles with a fashionable design and duo-spherical lens technology
- metal-free
- additional eyebrow protection with Eye Plus Protection: a bevelled edge in upper area
- soft, non-slip ear pieces (uvex duo Component technology) prevent pressure points
- very large field of vision
- can be easily combined with other PPE
- suitable for the uvex helmet IES (Integrated Eyewear System)

Technical details	
Frame	
Material	Front piece/Temple POM/TPE
Features	excellent ventilation
Colour	black-grey
Marking	
Manufacturer's ID code	W
Applicable EN norm	166
Low-energy impact	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,1 mm
Coating	supravison extreme
Colour	clear
UV protection	UV 400
Marking	
Filter	2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Low-energy impact	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight

30 g

Packing

5 spectacles per box

160 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 170

PPE Category

Category II