


**Product Datasheet model uvex pheos 9192 281**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

**Product  
characteristics**

- modern safety spectacles with a fashionable design and duo-spherical lens technology
- metal-free
- additional eyebrow protection with Eye Plus Protection: a bevelled edge in upper area
- soft, non-slip ear pieces (uvex duo Component technology) prevent pressure points
- very large field of vision
- can be easily combined with other PPE
- suitable for the uvex helmet IES (Integrated Eyewear System)

<b>Technical details</b>	
<b>Frame</b>	
Material	<b>Front piece/Temple</b> POM/TPE
Features	excellent ventilation
Colour	black-grey
<b>Marking</b>	
Manufacturer's ID code	W
Applicable EN norm	166
Low-energy impact	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
<b>Lens</b>	
Material	PC
Thickness	2,1 mm
Coating	supravison extreme
Colour	grey
UV protection	UV 400
<b>Marking</b>	
Filter	5-2,5 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Low-energy impact	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

**Miscellaneous**

Weight

30 g

Packing

5 spectacles per box

160 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 172

PPE Category

Category II