


**Product Datasheet model uvex pheos s blue 9192 726****UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth****Product  
characteristics**

- modern safety spectacles with a fashionable design and duo-spherical lens technology
- small version
- metal-free
- sustainable version using renewable plant raw materials
- additional eyebrow protection with Eye Plus Protection: a bevelled edge in upper are
- soft, non-slip ear pieces (uvex duo Component technology) prevent pressure points
- very large field of vision
- can be easily combined with other PPE
- suitable for the uvex helmet IES (Integrated Eyewear System)

<p><b>Technical details</b></p> <p><b>Frame</b>  Material  Features  Colour</p> <p>Manufacturer's ID code  Applicable EN norm  Low-energy impact  Resistance to high speed particles at extremes of temp.  Conformity symbol</p>	<p><b>Front piece/Temple</b></p> <p>PA/TPE (bio)  excellent ventilation  sand-blue</p> <p><b>Marking</b>  W  166  F (45 m/s)  T</p> <p>CE</p>
<p><b>Lens</b></p> <p>Material  Thickness  Coating  Colour  UV protection</p> <p>Filter  Manufacturer's ID code  Optical class  Low-energy impact  Resistance to high speed particles at extremes of temp.  Surface resistance to fine particles  Antifog  Conformity symbol  Factory symbol</p>	<p>PC (bio granule)  2,1 mm  uvex supravision excellence  clear  UV 400</p> <p><b>Marking</b>  2C-1,2 (DIN EN 170)  W  1  F (45 m/s)  T</p> <p>K</p> <p>N  CE</p> <p></p>

**Miscellaneous**

Weight

28 g

Packing

5 spectacles per box

160 spectacles per cardboard box

Standards

DIN EN 166 + DIN EN 170

PPE Category

Category II